## BOBC F Telcordi Super Trace Mos Trace Mos Trace E Series Se

	_	_		4000		_	_
			, <b>.</b>		~~		
-	_1		/ A TO				7
							- T

## Features

- Telcordia Compatible Software Included
   Super Simple Graphical User Interface
  - ◆ Trace Comparison with Trace Overlay
    - Most Affordable OTDR on the Market
    - Training with Onboard Help Screens
      - Event Table with Pass/Fail Feature
        - Onboard Memory for 1000 traces
        - Light Weight Rugged Enclosure
          - Easy To Read Color Display
            - Ultra Fast Trace Acquisition
              - SM and MM Units Available
                - Trouble Shooting with VFL
                  - 30 dB Dynamic Range
                    - Bright Color Display
                      - One Button Testing
                        - Short Dead Zone

| •    | √ KH         | SPLICE  | 2POINT  | DB/KH   | TVPE     |
|------|--------------|---------|---------|---------|----------|
| 1    | X 8.1948     | +1.344  | -8, 975 | -0.451  | -70.7    |
| 2    | × 8.3676     | TC 200  | +8.824  | +0.137  | -65.3    |
| 8    | X 8.5568     | +1.252  | +8.373  | +2, 181 | Sple     |
| 4    | × 8.9168     | +4, 856 | +8.814  |         | -        |
| 5    | X 8.9448     | +2, 646 | -8,965  | -0.057  | Solo     |
| Н    |              |         |         |         | -        |
| Н    |              | _       |         |         | $\vdash$ |
| Н    |              |         |         |         | -        |
| Н    |              |         |         |         | -        |
| н    |              |         |         |         |          |
| Е    | ₹ 8.9168     | -HA-    | +4.152  | +4. 654 | Link     |
| 100  | *1.468       |         | 1       |         | - 60     |
| 2    | -1559an      |         | ħ.      |         | 100      |
| DUC. |              |         |         |         | 100      |
|      | *Long        |         | 11      |         | 2.5      |
| EM.  | .3/          |         | -1[     |         |          |
| 105  | *10a         |         | 1       |         |          |
| Sen  | se Mt Splice | OL20 C  | RL (50) | Link (5 | Return   |
|      | .,           |         |         |         |          |

| Ever                                    |     | _  |    |   |
|---|-----|----|----|---|
| -1000                                   | ••• | -  | ы  | ~ |
|   | 11  | 12 | ги | - |
| _,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,, | 1.  | 14 | ы  | • |
|   |     |    |    |   |

| į |      |         | 1000   |     |      |        |          |    |
|---|------|---------|--------|-----|------|--------|----------|----|
|   | 888  | FISTEST | . 999  | 013 | FIST | EST. 0 | 818      |    |
|   | 881  | FISTEST | r. 881 | 814 | FIST | EST. 6 | 814      |    |
| ı | 882  | FISTEST | 1.882  | 915 | FIST | EST. 0 | 915      |    |
| 1 | 883  | FISTEST | 1.883  | 816 | FIST | EST. 0 | 816      |    |
| ı | 834  | FISTEST | 1.004  | 917 | FIST | EST. 0 | 917      |    |
| ı | 885  | FISTEST | 1.005  | 918 | FIST | EST. 0 | 918      |    |
| ı | 836  | FISTEST | 1.006  | 819 | FIST | EST. 0 | 919      |    |
| ı | 887  | FISTEST | T. 007 | 826 | FIST | E8T. 0 | 328      |    |
| ı | 998  | FISTEST | T. 008 | 82t | FIST | E8T. 0 | 321      |    |
| ı | 889  | FISTEST | T. 009 | 822 | FIST | EST. 6 | 322      |    |
| ı | 818  | FISTEST | T. 010 | 823 | FIST | EST. 6 | 828      |    |
| ı | 811  | FISTEST | T. 011 | 824 | FIST | EST. 6 | 324      |    |
| ı | 812  | FISTER  | T. 012 | 935 | FIST | E8T. 6 | 325      |    |
| ı | TOR  | =1.468  |        |     |      | 1.14   | и,       | 8  |
| ı | X    | :1818m  |        |     |      | 113    | Ħ:       | Ē  |
| ı | AVE  | *Long   | L .    |     |      | 1,14   | H        | 2  |
| ı | 24   | -2n     |        | _   |      | 쁘.     | $\sim$   | ũ, |
| 1 | 1000 | =1Kw    |        |     |      | H٢     | 핧비       | 6  |
| ı |      | -16.8   |        |     |      |        | <u>«</u> | ы  |
| ı | Ret  | um Copy | Name   | Del | Mark | Deal   | US       | 8  |
| • |      |         |        |     |      |        |          |    |

File Management

| Total Date: 50                 | 10 TR.       | _               |           | Specialist Ann      |                     |        |
|--------------------------------|--------------|-----------------|-----------|---------------------|---------------------|--------|
| WALL STREET                    | DOM: U.S.    |                 | _         | THE THE THE         | Table 1             |        |
| Self-Karber                    | 1000         |                 |           | Cases Type 707      |                     |        |
| Code 10:431                    |              |                 |           | Joseph Prom Prints  |                     |        |
| TOW IS NOT                     |              |                 |           | LEGBOY TO THE BOT   |                     |        |
|                                |              |                 |           |                     |                     |        |
| 1-1-200m<br>2-1000m<br>1-1000m |              | 5               | 200       | 20.7                | 100                 | in.    |
| H                              |              |                 |           |                     |                     |        |
|                                | _            | -               |           |                     |                     |        |
| -                              | _            |                 |           |                     |                     |        |
|                                | 200          | À.              |           |                     |                     |        |
|                                |              | -35             | -         | -                   |                     |        |
| 4                              |              |                 |           | THE PERSON NAMED IN | STATE OF THE PARTY. | واخطة  |
| 1                              |              |                 |           | -                   | شوالها              |        |
| 11:                            | -            |                 | 9.7       |                     | 100                 | 1.0    |
|                                |              |                 |           |                     |                     |        |
| 1000                           | 1717         | -               | 141 br 10 |                     |                     |        |
| water P                        | W TON        | -               | T Belle   | 1100                | T #RAGO             | I Fame |
|                                | m 527        | 100             | 100       | SCH #               | 120 M               | No.    |
| 1 1                            | a 836        | 100             | 100.00    | 446.4               | 8294.86             | 88.4   |
| -                              | <b>₩</b> €27 | 7 600           | 139-60    | THE                 | E379-80             | Specia |
|                                | W 125        | The Contract of | 128 60    | 600 M               | E-100-85            | Test   |
| 1                              |              | -               | MAX.      | 4.764.48            | 3.654.49            | Let    |
| i<br>tuan                      | was 129      | -               | -         |                     |                     |        |

Report Printout From Software Included With The BOBCAT OTDR



Fiber Optics For Sale Co.

408-945-6613 408-945-6613

1532 Centre Pointe Dr. Milpitas •FAX 408-273-6592 colin@fo4sale.com www.fiberoptics4sale.com

## BOBCAT OTDR

The BOBCAT OTDR is the most affordable Hand-Held OTDR on the Market today with all of the features of more expensive units. Features such as Trace Overlay, Visual Fault Locator, Color Display, One Button Autotest and Event Analysis are included. These are features one would expect to find on units costing thousands more. This OTDR can be operated by the novice while at the same time appreciated by the seasoned user.

This unit is available in dual singlemode, dual multimode and single wavelength versions. Testing is made simple and fast with the press of the Auto Test button. Examine the trace using the straight forward zoom feature and A/B cursor selection button. Zero in on events fast with the powerful Event Selection feature or with the event analysis table.

The BOBCAT OTDR's abundant dynamic range and a 2 meter dead zone, makes it ideal for links up to 240km as well as being perfect for short LAN links within the facility. Weighing in at less than two pounds, this OTDR is ideal for all conditions. The rubber boot with bail adds protection and provides the ideal angle for viewing the display while operating on a work bench.

Trace analysis and reporting is fast and easy with the Pass/Fail feature, onboard event table or the supplied Telcordia SR4731 compatible software with multi-trace capability. The OTDR has on board storage of 1000 traces with the ability to download traces directly to your computer via USB cable.

| Ordering Information: |                                |  |  |  |
|-----------------------|--------------------------------|--|--|--|
| OVP-850               | Multimode OTDR 850nm           |  |  |  |
| OVP-1300              | Multimode OTDR 1300nm          |  |  |  |
| OVP-8513              | Dual Multimode OTDR 850/1300nm |  |  |  |
| OVP-1310              | Singlemode OTDR 1310nm         |  |  |  |
| OVP-1550              | Singlemode OTDR 1550nm         |  |  |  |
| OVP-1315              | Singlemode OTDR 1310/1550nm    |  |  |  |
| OVP-HC                | Hard Carry Case                |  |  |  |
| OVP-BC                | Auxiliary Charger Kit          |  |  |  |

| OVP-OTDR Specific                 | cations:  |  |  |
|-----------------------------------|---|--|--|
| Wavelength                        | 850, 1300, 1310,1550, ±20nm   |  |  |
| Dynamic Range                     | 27/26dB MM, 30/29dB SM  |  |  |
| Pulse Width                       | 20 - 10,000 ns  |  |  |
| Units of Measurement              | km, kf  |  |  |
| Event Dead zone                   | 2m  |  |  |
| Attenuation Dead Zone             | 5m  |  |  |
| Resolution                        | .25 - 64m   |  |  |
| Distance Uncertainty              | ±(0.75m + 0.005% x distance + sampling resolution)  |  |  |
| Full Scale Distance Range         | 1-64km MM , 1-240km SM  |  |  |
| Typical Real-time Refresh Rate    | 4 Hz  |  |  |
| Group Index of Refraction (GIR)   | 1.024 - 2.048   |  |  |
| Linearity                         | ± .05 dB/dB   |  |  |
| Memory Capacity                   | 1000  |  |  |
| Memory Type                       | Internal  |  |  |
| Power Supply / Charger            | Universal   |  |  |
| Battery                           | 4hr   |  |  |
| Storage Temperature               | -20 to 60 C   |  |  |
| Operating Temperature Range       | -10 to 50 C   |  |  |
| Dimensions (without rubber boot ) | 7.62" L x 3.88" W x 1.56" H<br>(194mm L x 99mm W x 40mm H)  |  |  |
| Weight                            | 1.6 lbs   |  |  |
| Communications ports              | USB   |  |  |
| Connector Styles                  | FC, ST, SC Interchangeable  |  |  |
| Accessories Provided              | Universal Power Adapter w/US,<br>UK, Continental Europe, and Aus-<br>tralian Plugs, Interchangeable FC/<br>ST and SC Adapters, Windows/<br>Telcordia SR4731 Software, Rub-<br>ber Boot, USB Cable, Manual |  |  |

FIS Reserves the right to change specifications with out notice

| Visible Light Source |  |  |  |  |
|----------------------|--|--|--|--|
| Emitter Type         | Laser  |  |  |  |
| Wavelength           | 650nm ±5nm   |  |  |  |
| Laser Safety Class   | Class IIFDA21 CFR1040.10<br>&1040.11 IEC 825-1: 1993 |  |  |  |
| Connector Type       | 2.5mm Universal                                      |  |  |  |
| Output Power         | 1mW Max.   |  |  |  |

FIS Reserves the right to change specifications without notice