


McGRAW-HILL PROFESSIONAL ENGINEERING
SPIE PRESS



Modern Lens Design

Second Edition

- ✓ Detailed procedures for designing any major lens
- ✓ Demonstration design case studies
- ✓ Designing with lens design software

Warren J. Smith

Modern Lens Design

Warren J. Smith

*Chief Scientist
Kaiser Electro-Optics, Inc., Carlsbad, California
and Consultant in Optics and Design*

Second Edition

McGraw-Hill

New York Chicago San Francisco Lisbon London Madrid
Mexico City Milan New Delhi San Juan Seoul
Singapore Sydney Toronto

The McGraw-Hill Companies

Cataloging-in-Publication Data is on file with the Library of Congress.

Copyright © 2005, 1992 by The McGraw-Hill Companies, Inc. All rights reserved. Printed in the United States of America. Except as permitted under the United States Copyright Act of 1976, no part of this publication may be reproduced or distributed in any form or by any means, or stored in a data base or retrieval system, without the prior written permission of the publisher.

1 2 3 4 5 6 7 8 9 0 DOC/DOC 0 1 0 9 8 7 6 5 4

ISBN 0-07-143830-0

The sponsoring editor for this book was Stephen S. Chapman and the production supervisor was Pamela A. Pelton. It was set in Century Schoolbook by International Typesetting and Composition. The art director for the cover was Anthony Landi.

Printed and bound by RR Donnelley.



This book was printed on recycled, acid-free paper containing a minimum of 50% recycled, de-inked fiber.

McGraw-Hill books are available at special quantity discounts to use as premiums and sales promotions, or for use in corporate training programs. For more information, please write to the Director of Special Sales, McGraw-Hill Professional, Two Penn Plaza, New York, NY 10121-2298. Or contact your local bookstore.

Information contained in this work has been obtained by The McGraw-Hill Companies, Inc. ("McGraw-Hill") from sources believed to be reliable. However, neither McGraw-Hill nor its authors guarantee the accuracy or completeness of any information published herein, and neither McGraw-Hill nor its authors shall be responsible for any errors, omissions, or damages arising out of use of this information. This work is published with the understanding that McGraw-Hill and its authors are supplying information but are not attempting to render engineering or other professional services. If such services are required, the assistance of an appropriate professional should be sought.

These aberrations are related by:

$$TA = LA \cdot \tan U$$

$$AA = TA/l'$$

$$OPD = |AA|$$

The *optical path* ($OP = \sum n \cdot d$) is related to the time of travel of light, which is equal to $\sum n \cdot d/c$. Ideally the OP from the object point to a reference sphere centered on the image point (and often located at the exit pupil—or at infinity) should be constant over the full aperture. The *optical path difference*, $OPD = (OP_{\text{ray}} - OP_{\text{ref}})$, where OP_{ray} is the path along a ray and OP_{ref} is the path along the axis or along the principal ray. The *pupil function* is $OPD(x, y)$; the *wave (front) function* is $w(x, y) = OPD(x, y)/\lambda$ in waves; and the *phase function* $\Phi(x, y)$ is $2\pi w(x, y)$ in radians.

Aberrations may be *intrinsic* or *induced*. The intrinsic aberrations are those of a surface (or element) that are unaffected by the aberrations of the other surfaces. Induced aberrations are created by the aberrations (i.e., changes in the ray heights or angles) of the other elements. Usually the lower-order aberrations of the other surfaces cause induced higher-order aberrations. For example, the third-order aberrations of preceding surfaces will induce fifth-order spherical in following surfaces. See Chap. 6, Secs. 6.3 and 6.4 for an example of how the third-order spherical and first-order chromatic aberration in the first element affect the zonal (fifth-order) spherical and spherochromatic of the lens.

5.4 Scaling a Design, Its Aberrations, and its Modulation Transfer Function

A lens prescription can be scaled to any desired focal length simply by multiplying all of its dimensions by the same constant. All of the *linear* aberration measures will then be scaled by the same factor. Note, however, that percent distortion, *chromatic difference of magnification* (CDM), the numerical aperture or *f* number, the aberrations expressed as angular aberrations, and any other *angular* characteristics remain completely unchanged by scaling.

The exact *diffraction modulation transfer function* (MTF) cannot be scaled with the lens data. The diffraction MTF, since it includes diffraction effects that depend on wavelength, will not scale because the wavelength is not ordinarily scaled with the lens. A *geometric* MTF can be scaled by dividing the spatial frequency ordinate of the MTF plot by the scaling factor. Of course, because it neglects diffraction, the geometric